


**Vue d'ensemble**

- Male straight
- M8 , 4-pole, A-coded
- 0,14 - 0,34mm<sup>2</sup>, 2,5 - 5,1mm



**Caractéristiques techniques**

| Side A                     |                      | Side A                        |                      |
|----------------------------|----------------------|-------------------------------|----------------------|
| Head A: Connection         | M8                   | Wire cross section (min.)     | 0,14 mm <sup>2</sup> |
| Head A: Angle cable outlet | 0°                   | Cable diameter (max.)         | 5,1 mm               |
| Head A: Gender             | Male                 | Cable diameter (min.)         | 2,5 mm               |
| Head A: Shielded           | No                   | <b>Données électriques</b>    |                      |
| Head A: No. of poles       | 4                    | Operating voltage             | max. 32 V DC         |
| Head A: Width across flats | AF9                  | Operating current per contact | max. 4 A             |
| Head A: Tightening torque  | 0,4 Nm               | <b>Données mécaniques</b>     |                      |
| Min. AWG                   | 26                   | Head A: Degree of protection  | IP67                 |
| Max. AWG                   | 22                   | <b>Conditions ambiantes</b>   |                      |
| Connection method          | IDC terminal         | Head A: Pollution degree      | 3                    |
| Wire cross section (max.)  | 0,34 mm <sup>2</sup> |                               |                      |