

**Vue d'ensemble**

- Female straight
- M8 , 4-pole, A-coded
- 0,14 - 0,5mm<sup>2</sup>, 4 - 5,5mm, shielded



**Caractéristiques techniques**

**Side A**

Head A: Connection	M8
Head A: Angle cable outlet	0°
Head A: Gender	Female
Head A: Shielded	Oui
Head A: No. of poles	4
Head A: Tightening torque	0,4 Nm
Min. AWG	26
Max. AWG	20
Connection method	Screw terminals
Wire cross section (max.)	0,5 mm <sup>2</sup>
Wire cross section (min.)	0,14 mm <sup>2</sup>

**Side A**

Cable diameter (max.)	5,5 mm
Cable diameter (min.)	4 mm

**Données électriques**

Operating voltage	max. 50 V DC
Operating current per contact	max. 4 A

**Données mécaniques**

Head A: Degree of protection	IP67
------------------------------	------

**Conditions ambiantes**

Head A: Pollution degree	3
--------------------------	---