

ESG 34AB0200G

Connector M12, 4 pin, straight, 2 m, shielded

Article number: 11164785

Overview

- For railway applications
- 4 pin versions shielded
- Cable coating RADOX
- Cabel according EN 45545-2



Picture similar

Technical data

General data

Type (head 1)	Straight
Dimension (head 1)	M12
Length	2 m
Material cable jacket	RADOX
Number of positions	4 pins
Shielding	Shielded
Protection class	IP 65

General data

Usage	Connecting cable for Connector type M12
-------	---

General data

Connection type (head 1)	Connector female
Dimension (head 1)	M12
Type (head 1)	Straight
Connection type (head 2)	Free cable end
Particular characteristics	Railway industry
Shielding	Shielded
Material cable jacket	RADOX
Length	2 m
Number of positions	4 pins
Protection class	IP 65

Dimension drawing



Pin assignment

