

# Obj Kowa LM25XC 25mm/f2,0

Article number: 11092593

## Overview

- Kowa lens
- 25 mm
- F 2,0-16
- format 4/3"
- M.O.D. 0,15 m
- C-mount



Picture similar

## Technical data

### General data

Manufacturer Kowa

### Mechanical data

Lens mount C-mount

Dimensions 45 mm × 89 mm

Max. outer diameter 45 mm (without knurled screws)

55 mm (with knurled screws)

Max. length (excl. thread) 89 mm

Weight ≤ 250 g

Filter thread M 40,5 × 0,5

### Lens data

Lens resolution 26 MP

Pixel resolution 3 μm

### Lens data

Focal length 25 mm

Format 4/3"

Aperture F2,0-16

Aperture control Manual

M.O.D. 0.15 m

Horizontal angle of view 40.9 °

Vertical angle of view 31.1 °

Diagonal angle of view 50.2 °

At image format 13,8 × 18,4 mm

### Environmental conditions

Operating temperature -10 ... +50 °C