


Obj Kowa LM35XC 35mm/f2,0

Article number: 11092597

Overview

- Kowa lens
- 35 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,2 m
- C-mount



Picture similar

Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount

Dimensions 45 mm × 74 mm

Max. outer diameter 45 mm (without knurled screws)

55 mm (with knurled screws)

Max. length (excl. thread) 74 mm

Weight ≤ 210 g

Filter thread M 37,5 × 0,5

Lens data

Lens resolution 26 MP

Pixel resolution 3 μm

Lens data

Focal length 35 mm

Format 4/3"

Aperture F2,0-16

Aperture control Manual

M.O.D. 0.2 m

Horizontal angle of view 22.4 °

Vertical angle of view 29.6 °

Diagonal angle of view 36.6 °

At image format 13,8 × 18,4 mm

Environmental conditions

Operating temperature -10 ... +50 °C