

Overview

- Network Adapter RJ45 to USB, 100 MBit/s



Technical data

Side A

Head A: Connection	RJ45
Head A: Angle cable outlet	0°
Head A: Gender	Female

Side B

Head B: Connection	USB Type-A
Head B: Angle cable outlet	0°
Head B: Gender	Male

Cables

Cable length	30 mm
External sheath: Color	Black

Cable

Transmission rate	100 MBit/s
Cable length	30 mm
External sheath: Color	Black

Environmental conditions

Temperature range (fixed)	approx. 10 ...+ 40 °C
---------------------------	-----------------------