

## Overview

- Carl Zeiss lens
- 8 mm
- F 2,8-22
- format 4/3"
- M.O.D. 0,102 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Carl Zeiss

### Mechanical data

Lens mount C-mount

Dimensions 86 mm × 63 mm

Max. outer diameter 86 mm (without knurled screws)  
86 mm (with knurled screws)

Max. length (excl. thread) 63 mm

Weight ≤ 376 g

Filter thread M 72,0 × 0,75

### Lens data

Lens resolution 20 MP

Pixel resolution 2 μm

Focal length 8 mm

Format 4/3"

Aperture F2,8-22

Aperture control Manual

M.O.D. 0.102 m

### Environmental conditions

Operating temperature -22 ... +55 °C