

**Overview**

- Ricoh Imaging lens
- 12 mm
- F 2.0-16
- format 1,1"
- M.O.D. 0.08 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

**Technical data**

**General data**

Manufacturer Ricoh Imaging

**Mechanical data**

Lens mount C-mount  
 Dimensions 42 mm × 57,5 mm  
 Max. outer diameter 42 mm (without knurled screws)  
 52 mm (with knurled screws)  
 Max. length (excl. thread) 60.5 mm  
 Weight ≤ 156 g

**Mechanical data**

Filter thread M 40,5 × 0,5

**Lens data**

Lens resolution 12 MP  
 Focal length 12 mm  
 Format 1,1"  
 Aperture F2.0-16  
 Aperture control Manual  
 M.O.D. 0.08 m