

ZVL-FL-BC7528-9M

Article number: 11154328

Overview

- Ricoh Imaging lens
- 75 mm
- F 2,8-32
- format 1,1"
- M.O.D. 0,25 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount
 Dimensions 42 mm × 81,0 mm
 Max. outer diameter 42 mm (without knurled screws)
 52 mm (with knurled screws)
 Max. length (excl. thread) 81 mm
 Weight ≤ 189 g

Mechanical data

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 12 MP
 Focal length 75 mm
 Format 1,1"
 Aperture F2,8-32
 Aperture control Manual
 M.O.D. 0.25 m