

# ZVL-FL-CC1614A-2M

Article number: 11150228

## Overview

- Ricoh Imaging lens
- 16 mm
- F 1,4-16
- format 2/3"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Ricoh Imaging

### Mechanical data

Lens mount C-mount

Dimensions 29,5 mm × 32,2 mm

Max. outer diameter 29.5 mm (without knurled screws)  
39.5 mm (with knurled screws)

Max. length (excl. thread) 32.2 mm

Weight ≤ 54 g

### Mechanical data

Filter thread M 27,0 × 0,5

### Lens data

Lens resolution 2 MP

Focal length 16 mm

Format 2/3"

Aperture F1,4-16

Aperture control Manual

M.O.D. 0.1 m