

ZVL-FL-CC5024A-2M

Article number: 11150230

Overview

- Ricoh Imaging lens
- 50 mm
- F 2,4-22
- format 2/3"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount
 Dimensions 32 mm × 46,5 mm
 Max. outer diameter 32 mm (without knurled screws)
 42 mm (with knurled screws)
 Max. length (excl. thread) 46.5 mm
 Weight ≤ 66 g

Mechanical data

Filter thread M 30,5 × 0,5

Lens data

Lens resolution 2 MP
 Focal length 50 mm
 Format 2/3"
 Aperture F2,4-22
 Aperture control Manual
 M.O.D. 0.3 m