

ZVL-FL-CC5028-2M

Article number: 11012785

Overview

- Ricoh Imaging lens
- 50 mm
- F 2,8-22
- format 2/3"
- M.O.D. 0,9 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Ricoh Imaging

Mechanical data

Lens mount C-mount

Dimensions 29,5 mm × 34,0 mm

Max. outer diameter 29.5 mm (without knurled screws)
39.5 mm (with knurled screws)

Max. length (excl. thread) 34 mm

Weight ≤ 55 g

Filter thread M 27,0 × 0,5

Lens data

Lens resolution 2 MP

Lens data

Focal length 50 mm

Format 2/3"

Aperture F2,8-22

Aperture control Manual

M.O.D. 0.9 m

Horizontal angle of view 10.1 °

Vertical angle of view 7.6 °

Diagonal angle of view 12.5 °

At image format 8,8 × 6,6 mm

Environmental conditions

Operating temperature -20 ... +50 °C