

Overview

- Kowa lens
- 16 mm
- F 1,8-16
- format 1,1"
- M.O.D. 0,1 m
- C-mount



Picture similar

Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount

Dimensions 43 mm × 72,2 mm

Max. outer diameter 43 mm (without knurled screws)
53 mm (with knurled screws)

Max. length (excl. thread) 65.7 mm

Weight ≤ 200 g

Filter thread M 35,5 × 0,5

Lens data

Lens resolution 24 MP

Lens data

Focal length 16 mm

Format 1,1"

Aperture F1,8-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 48.0 °

Vertical angle of view 36.7 °

Diagonal angle of view 58.3 °

At image format 10,6 × 14,1 mm

Environmental conditions

Operating temperature -10 ... +50 °C