

ZVL-LM3NCM 3,5mm/f2,4

Article number: 11116658

Overview

- Kowa lens
- 3,5 mm
- F 2,4-14
- format 1/1.8"
- M.O.D. 0,1 m
- C-mount



Picture similar

Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount
 Dimensions 42 mm × 38,2 mm
 Max. outer diameter 42 mm (without knurled screws)
 52 mm (with knurled screws)
 Max. length (excl. thread) 38.2 mm
 Weight ≤ 85 g

Mechanical data

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 2 MP
 Focal length 3.5 mm
 Format 1/1.8"
 Aperture F2,4-14
 Aperture control Manual
 M.O.D. 0.1 m