

**Overview**

- Kowa lens
- 6,5 mm
- F 2,5-16
- format 1,1"
- M.O.D. 0,1 m
- C-mount



*Picture similar*

**Technical data**

**General data**

Manufacturer Kowa

**Mechanical data**

Lens mount C-mount

Dimensions 84 mm × 86,1 mm

Max. outer diameter 84 mm (without knurled screws)  
84 mm (with knurled screws)

Max. length (excl. thread) 79.1 mm

Weight ≤ 310 g

Filter thread M 82 × 0,75

**Lens data**

Lens resolution 24 MP

**Lens data**

Focal length 6.5 mm

Format 1,1"

Aperture F2,5-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 95.7 °

Vertical angle of view 78.7 °

Diagonal angle of view 109.1 °

At image format 10,6 × 14,1 mm

**Environmental conditions**

Operating temperature -10 ... +50 °C