

ZVL-LSF3528-U58

Article number: 11205385

Overview

- Myutron lens
- 35 mm
- F 2,8-22
- format 44 mm
- M.O.D. 0,23 m
- locating screw for aperture and focus
- M58-mount
- focal flange distance 12 mm



Picture similar

Technical data

General data

Manufacturer Myutron

Mechanical data

Lens mount M58-mount

Dimensions 62 mm × 123 mm

Max. outer diameter 62 mm (without knurled screws)
62 mm (with knurled screws)

Max. length (excl. thread) 118 mm

Weight ≤ 416 g

Filter thread M 52,0 × 0,75

Lens data

Lens resolution 48 MP (suitable for 65 MP)

Focal length 35 mm

Format 44 mm

Aperture F2.8-22

Aperture control Manual

M.O.D. 0.23 m

Environmental conditions

Operating temperature 0 ... +40 °C