

## ZVL-M3528-MPW3

Article number: 11704874

### Overview

- Computar lens
- 35 mm
- F 2,8-16
- format 2/3"
- M.O.D. 0,25 m
- locating screw for aperture and focus
- C-mount



Picture similar

### Technical data

#### General data

Manufacturer Computar

#### Mechanical data

Lens mount C-mount

Dimensions 29 mm × 38,5 mm

Max. outer diameter 29 mm (without knurled screws)

Max. length (excl. thread) 39 mm

Weight ≤ 48 g

Filter thread M 27 × 0,5

#### Lens data

Lens resolution 6 MP

Pixel resolution 2.74 μm

#### Lens data

Focal length 35 mm

Format 2/3"

Aperture F2.8-16

Aperture control Manual

M.O.D. 0.25 m

Horizontal angle of view 14.3 °

Vertical angle of view 10.8 °

Diagonal angle of view 17.9 °

At image format 8,8 × 6,6 mm

#### Environmental conditions

Operating temperature -10 ... +50 °C