

**Overview**

- Computar lens
- 8 mm
- F 2,6-16
- format 1"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Picture similar

**Technical data**

**General data**

Manufacturer           Computar

**Mechanical data**

Lens mount            C-mount

Dimensions           69,5 mm × 52,93 mm

Max. outer diameter   69.5 mm (without knurled screws)  
69.5 mm (with knurled screws)

Max. length (excl. thread) 55.23 mm

Weight                ≤ 203 g

**Lens data**

Lens resolution       20 MP

Focal length           8 mm

**Lens data**

Format                1"

Aperture             F2,6-16

Aperture control     Manual

M.O.D.                0.1 m

Horizontal angle of view 76.9 °

Vertical angle of view 61.5 °

Diagonal angle of view 88.8 °

At image format     12,8 × 9,6 mm

**Environmental conditions**

Operating temperature -10 ... +50 °C