

ZVL-V1624-MPZ

Article number: 11700366

Overview

- Computar lens
- 16 mm
- F 2,4-16
- format 1"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount

Dimensions 39,5 mm × 54,4 mm

Max. outer diameter 39.5 mm (without knurled screws)
49.5 mm (with knurled screws)

Max. length (excl. thread) 49.09 mm

Weight ≤

Filter thread M 35,5 × 0,5

Lens data

Lens resolution 20 MP

Lens data

Focal length 16 mm

Format 1"

Aperture F2,4-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 43.8 °

Vertical angle of view 33.6 °

Diagonal angle of view 53.2 °

At image format 12,8 × 9,6 mm

Environmental conditions

Operating temperature -10 ... +50 °C