

Overview

- Computar lens
- 16 mm
- F 2,8-16
- format 1,1"
- M.O.D. 0,3 m
- locating screw for aperture and focus
- C-mount



Picture similar

Technical data

General data

Manufacturer Computar

Mechanical data

Lens mount C-mount

Dimensions 39,5 mm × 32,2 mm

Max. outer diameter 39.5 mm (without knurled screws)
49.5 mm (with knurled screws)

Max. length (excl. thread) 36.35 mm

Weight ≤ 92 g

Filter thread M 34,0 × 0,5

Lens data

Lens resolution 12 MP

Lens data

Focal length 16 mm

Format 1,1"

Aperture F2,8-16

Aperture control Manual

M.O.D. 0.3 m

Horizontal angle of view 48.2 °

Vertical angle of view 36.2 °

Diagonal angle of view 57.9 °

At image format 26 × 19 mm

Environmental conditions

Operating temperature -10 ... +50 °C