

Product	Shaft	Pulses per revolution, output	Connection	Comment	Material number
HOG1070	Solid shaft ø11 mm	Parameterization at factory <sup>1)</sup>	2 x Cable gland M20	Redundant – Manipulation proof	EHOG1070-11731291
		Parameterization & monitoring at customer	2 x Cable gland M20	SMART, redundant	EHOG1070-11731290
	Blind hollow shaft ø16G7 mm	Parameterization at factory <sup>1)</sup>	2 x Cable gland M20	Redundant – Manipulation proof	EHOG1070-11731292
		Parameterization & monitoring at customer	2 x Cable gland M20	SMART, redundant	EHOG1070-11731293

1) Please choose 2x resolution, output stage and zero pulse (length and position) with your order

Resolution: 1...32768 ppr

Output stage: HTL-P or TTL

Zero pulse:

- 90°, K1=K2=1

- 180°, K1=0

- 180°, K2=0

- 180°, K1=1

Example for EHOG1070-11731292: encoder 1: 5000 ppr, TTL, 180°, K2=0 / encoder 2: 1024 ppr, HTL, 90°, K1=K2=1