

Product	Shaft	Pulses per revolution, output	Connection	Comment	Material number
HOG1095	Solid shaft ø11 mm	1024, HTL-P	2 x Cable gland M20	Manipulation proof FSL	EHO1095-11731298
		2048, HTL-P	2 x Cable gland M20	Manipulation proof FSL	EHO1095-11731299
		Parameterization at factory <sup>1)</sup>	2 x Cable gland M20	Manipulation proof FSL	EHO1095-11731300
	Blind hollow shaft ø16G7 mm	1024, HTL-P	2 x Cable gland M20	Manipulation proof FSL	EHO1095-11731301
		2048, HTL-P	2 x Cable gland M20	Manipulation proof FSL	EHO1095-11731302
		Parameterization at factory <sup>1)</sup>	2 x Cable gland M20	Manipulation proof FSL	EHO1095-11731303

1) Please choose resolution, output stage and zero pulse (length and position) with your order

Resolution: 1...32768 ppr

Output stage: HTL-P or TTL

Zero pulse:

- 90°, K1=K2=1

- 180°, K1=0

- 180°, K2=0

- 180°, K1=1

Example for EHO1095 - 11731300: 5000 ppr, TTL, 180°, K2=0