

Connector M23 (S2BG17), 10 m cable (ATD)

Article number: 11070264

Overview

- Shielded connection cable with M23-female connector (17-pin) and wire end sleeves for ATD



Technical data

Cable specifications

Material	Cable sheath: SABIX® grey, halogen free
Weight approx.	920 g
Cable length	10 m

Cable specifications


Operating temperature	-20...+85 °C
Outer diameter	≈ 8.2 mm
Connection	Connector M23, 17-pin

Terminal assignment

Connector S2BG17	Core colour
Pin 1	white
Pin 2	brown
Pin 3	green
Pin 4	yellow
Pin 5	–
Pin 6	–
Pin 7	grey
Pin 8	pink
Pin 9	–
Pin 10	black
Pin 11	red
Pin 12	blue
Pin 13	–
Pin 14	white/green
Pin 15	brown/green
Pin 16	white/yellow
Pin 17	yellow/brown
Housing/shield	transparent

Dimensions

connector type 2,
bush contacts, straight,
17-pin
S2BG17



Suitable for

ATD 2S A 4 Y 7, ATD 2S B14 Y23, ATD 4S A 4 Y10

