

Overview

- universal power supply 24V/1,0A international with adapters for EU, US, UK, AU, KR



Picture similar

Technical data

Electrical data

Input	adapter: EU, US, UK, AU, KR (changeable)
Input voltage	90 VAC .. 264 VAC
Frequency	47 Hz .. 63 Hz
Output	M8/3-pin
Operating voltage	24 VDC
Current	1 A
Tolerance	5 %
Ripple	240 mV p-p
Level of efficiency	Level VI

Electrical data

Max. performance	24 W
------------------	------

Mechanical data

Dimensions	93,5 mm × 46,0 mm × 36,2 mm
Cable length [m]	1.8 m
Weight	≤ 170 g
Material	plastic

Environmental conditions

Operating temperature	0 ... +40 °C
Storage temperature	-20 ... +85 °C
Humidity	8 ... 90 % (non-condensing)