

Overview

- Male straight
- M8, 4-pole, A-coded
- 0,14 - 0,5mm², 4 - 5,5mm, shielded



Technical data

Side A		Side A	
Head A: Connection	M8	Cable diameter (max.)	5.5 mm
Head A: Angle cable outlet	0°	Cable diameter (min.)	4 mm
Head A: Gender	Male	Electrical data	
Head A: Coding	A	Operating current per contact	max. 4 A
Head A: Shielded	Yes	Mechanical data	
Head A: No. of poles	4	Head A: Degree of protection	IP67
Head A: Tightening torque	0.4 Nm	Environmental conditions	
Min. AWG	26	Head A: Pollution degree	3
Max. AWG	20	Commercial data	
Connection method	Screw terminals	Eclass	27440102
Wire cross section (max.)	0.5 mm ²		
Wire cross section (min.)	0.14 mm ²		

2024-06-25 The product features and technical data specified do not express or imply any warranty. Technical modifications subject to change.