

Vue d'ensemble

- Side A: Wires with Crimp contacts; Side B: Wires with Crimp contacts and shielding with Crimp contacts
- Cable structure: 8 x 0,34 mm²
- TPE; suitable for Food & Beverage
- Good resistance against chemicals and UV
- Halogen free



Caractéristiques techniques

Side A	
Side A: Shielding length	72 mm
Side A: Shielding processing	Not processed
Side A: Crimp terminal wire 1	0.34 mm ² ; contact length: 6 mm; isolated
Side A: Crimp terminal wire 2	0.34 mm ² ; contact length: 6 mm; isolated
Side A: Crimp terminal wire 3	0.34 mm ² ; contact length: 6 mm; isolated
Side A: Crimp terminal wire 4	0.34 mm ² ; contact length: 6 mm; isolated
Side A: Crimp terminal wire 5	0.34 mm ² ; contact length: 6 mm; isolated
Side B	
Side B: Shielding length	100 mm
Side B: Shielding processing	Twisted and reduced to 0.34 mm ²
Side B: Shielding crimp terminal	0.34 mm ² ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 1	0.34 mm ² ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 2	0.34 mm ² ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 3	0.34 mm ² ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 4	0.34 mm ² ; contact length: 6 mm; isolated
Side B: Crimp terminal wire 5	0.34 mm ² ; contact length: 6 mm; isolated
Cables	
Cable length	200 cm
Length tolerance	+ 10 cm
No. of wires	8
Shielded	Oui

Cables	
External sheath: Material	TPE
External sheath: Color	Black
Cable diameter	7,8 mm
Wire cross section	0,34 mm ²
Cable	
Cable: Temperature range (mobile)	- 40 ...+ 90 °C
Cable: Temperature range (fixed)	- 50 ...+ 90 °C
Operating voltage (only UL listed)	30 V AC/DC
Shielded	Oui
Length tolerance	+ 10 cm
Cable length	200 cm
Bending radius (fixed)	min. 4 × outer diameter
Bending radius (mobile)	min. 10 × outer diameter
Cable weight	127 g/m
Cable diameter	7,8 mm
External sheath: Material	TPE
Shielding: Material	Copper, tinned
Wire cross section	0,34 mm ²
External sheath: Color	Black
Données électriques	
Operating voltage (only UL listed)	30 V AC/DC
Données mécaniques	
Bending radius (mobile)	min. 10 × outer diameter
Bending radius (fixed)	min. 4 × outer diameter
Conditions ambiantes	
Cable: Temperature range (fixed)	- 50 ...+ 90 °C
Cable: Chemical resistance	ECOLAB material resistance test passed

Dessin d'encombrement

