

Vue d'ensemble

- Female straight
- M8, 3-pole, A-coded
- 0,14 - 0,5mm², 4 - 5,5mm, shielded



Caractéristiques techniques

Side A		Side A	
Head A: Connection	M8	Wire cross section (min.)	0,14 mm ²
Head A: Angle cable outlet	0°	Cable diameter (max.)	5,5 mm
Head A: Gender	Female	Cable diameter (min.)	4 mm
Head A: Coding	A	Données électriques	
Head A: Shielded	Oui	Operating current per contact	max. 4 A
Head A: No. of poles	3	Données mécaniques	
Head A: Tightening torque	0,4 Nm	Head A: Degree of protection	IP67
Min. AWG	26	Conditions ambiantes	
Max. AWG	20	Head A: Pollution degree	3
Connection method	Screw terminals		
Wire cross section (max.)	0,5 mm ²		