

ZVL-Rodagon-F_40mm_f5.6

Article number: 11201893

Overview

- Linos lens
- 40 mm
- f 5,6
- format 44 mm
- M.O.D. 0,094 m
- locating screw for focus
- F-mount



Picture similar

Technical data

General data

Manufacturer Linos

Mechanical data

Lens mount F-Mount

Dimensions 59 mm × 45.9 mm

Max. outer diameter 59 mm (without knurled screws)
69 mm (with knurled screws)

Max. length (excl. thread) 45.9 mm

Weight ≤ 150 g

Mechanical data

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 48 MP

Focal length 40 mm

Format 44 mm

Aperture f 5,6

Aperture control Manual

M.O.D. 0.094 m