

ZVL-Varioptic_C-C-39N0-160-R33

Article number: 11207011

Overview

- Corning® Varioptic® lens
- 16 mm
- F 2.8
- format 2/3"
- M.O.D. 0.11 m
- C-mount
- UART interface (3.3 V, 100 mA)



Picture similar

Technical data

General data

Manufacturer Corning

Mechanical data

Lens mount C-mount

Dimensions 36 mm × 38 mm

Max. outer diameter 36 mm

Max. length (excl. thread) 38 mm

Weight ≤ 99 g

Lens data

Lens resolution 5 MP

Focal length 16 mm

Format 2/3"

Aperture F2,8

Aperture control fix

M.O.D. 0.11 m

Diagonal angle of view 38 °

Environmental conditions

Operating temperature 0 ... +50 °C