

## Overview

- Carl Zeiss lens
- 12 mm
- F 2,0-22
- format 4/3"
- M.O.D. 0,101 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer Carl Zeiss

### Mechanical data

Lens mount C-mount

Dimensions 57 mm × 60 mm

Max. outer diameter 57 mm (without knurled screws)

64 mm (with knurled screws)

Max. length (excl. thread) 60 mm

Weight ≤ 264 g

Filter thread M 43,0 × 0,75

### Lens data

Lens resolution 20 MP

Pixel resolution 2 μm

Focal length 12 mm

Format 4/3"

Aperture F2,0-22

Aperture control Manual

M.O.D. 0.101 m

### Environmental conditions

Operating temperature -22 ... +55 °C