

Overview

- Kowa lens
- 12 mm
- F 1,8-16
- format 1,1"
- M.O.D. 0,1 m
- C-mount



Picture similar

Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount

Dimensions 51 mm × 79,8 mm

Max. outer diameter 51 mm (without knurled screws)
52 mm (with knurled screws)

Max. length (excl. thread) 73.8 mm

Weight ≤ 260 g

Filter thread M 49 × 0,75

Lens data

Lens resolution 24 MP

Lens data

Focal length 12 mm

Format 1,1"

Aperture F1,8-16

Aperture control Manual

M.O.D. 0.1 m

Horizontal angle of view 60.0 °

Vertical angle of view 46.9 °

Diagonal angle of view 71.0 °

At image format 10,6 × 14,1 mm

Environmental conditions

Operating temperature -10 ... +50 °C