

Overview

- Kowa lens
- 35 mm
- F 1,8-16
- format 1,1"
- M.O.D. 0,2 m
- C-mount



Picture similar

Technical data

General data

Manufacturer Kowa

Mechanical data

Lens mount C-mount

Dimensions 45 mm × 71,6 mm

Max. outer diameter 45 mm (without knurled screws)
55 mm (with knurled screws)

Max. length (excl. thread) 66 mm

Weight ≤ 205 g

Filter thread M 40,5 × 0,5

Lens data

Lens resolution 24 MP

Lens data

Focal length 35 mm

Format 1,1"

Aperture F1,8-16

Aperture control Manual

M.O.D. 0.2 m

Horizontal angle of view 22.1 °

Vertical angle of view 16.7 °

Diagonal angle of view 27.5 °

At image format 10,6 × 14,1 mm

Environmental conditions

Operating temperature -10 ... +50 °C