

# ZVL-Canon\_EF\_50mm f/1.8\_STM

Article number: 11703230

## Overview

- Canon lens
- 50 mm
- f 1.8 - 22
- format 43 mm
- STM auto focus (focus control: manual/automatic)
- Canon EF-mount



*Picture similar*

## Technical data

### General data

Manufacturer Canon

### Mechanical data

Lens mount Canon EF-mount  
 Dimensions 69.2 mm × 39.3 mm  
 Max. outer diameter 70 mm (without knurled screws)  
 Max. length (excl. thread) 39.3 mm  
 Weight ≤ 160 g  
 Filter thread M 49

### Lens data

Lens resolution 65 MP  
 Focal length 50 mm  
 Format 43 mm  
 Aperture f 1,8 - 22  
 Aperture control manual / automatic  
 Horizontal angle of view 40 °  
 Vertical angle of view 27 °  
 Diagonal angle of view 46 °