

## Overview

- Computar lens
- 12 mm
- F 2,6-16
- format 1"
- M.O.D. 0,1 m
- locating screw for aperture and focus
- C-mount



*Picture similar*

## Technical data

### General data

Manufacturer            Computar

### Mechanical data

Lens mount              C-mount

Dimensions             39 mm × 51,4 mm

Max. outer diameter    39 mm (without knurled screws)  
49 mm (with knurled screws)

Max. length (excl. thread) 43.5 mm

Weight                    ≤ 98.4 g

Filter thread             M 37,5 × 0,5

### Lens data

Lens resolution         20 MP

### Lens data

Focal length             12 mm

Format                    1"

Aperture                 F2,6-16

Aperture control        Manual

M.O.D.                    0.1 m

Horizontal angle of view 56.7 °

Vertical angle of view   44.1 °

Diagonal angle of view 67.4 °

At image format         12,8 × 9,6 mm

### Environmental conditions

Operating temperature   -10 ... +50 °C