

Product	Shaft	Pulses per revolution, output	Connection	Comment	Material number
HOG860	Solid shaft ø11 mm	1024, HTL-P	1 x cable gland M20	Manipulation proof	EHO860-11730669
			1 x flange connector M23	Manipulation proof	EHO860-11730670
		2048, HTL-P	1 x cable gland M20	Manipulation proof	EHO860-11730672
			1 x flange connector M23	Manipulation proof	EHO860-11730673
		Parameterization at factory ¹⁾	1 x cable gland M20	Manipulation proof	EHO860-11730674
			1 x flange connector M23	Manipulation proof	EHO860-11730675
	Parameterization & monitoring at customer	1 x cable gland M20	SMART	EHO860-11730676	
		1 x flange connector M23	SMART	EHO860-11730677	
	Blind hollow shaft ø12G7 mm	1024, HTL-P	1 x cable gland M20	Manipulation proof	EHO860-11730678
			1 x flange connector M23	Manipulation proof	EHO860-11730679
		2048, HTL-P	1 x cable gland M20	Manipulation proof	EHO860-11730680
			1 x flange connector M23	Manipulation proof	EHO860-11730681
		Parameterization at factory ¹⁾	1 x cable gland M20	Manipulation proof	EHO860-11730682
			1 x flange connector M23	Manipulation proof	EHO860-11730683
	Parameterization & monitoring at customer	1 x cable gland M20	SMART	EHO860-11730684	
		1 x flange connector M23	SMART	EHO860-11730685	
	Blind hollow shaft ø16G7 mm	1024, HTL-P	1 x cable gland M20	Manipulation proof	EHO860-11730686
			1 x flange connector M23	Manipulation proof	EHO860-11730687
		2048, HTL-P	1 x cable gland M20	Manipulation proof	EHO860-11730688
			1 x flange connector M23	Manipulation proof	EHO860-11730689
		Parameterization at factory ¹⁾	1 x cable gland M20	Manipulation proof	EHO860-11730690
			1 x flange connector M23	Manipulation proof	EHO860-11730691
	Parameterization & monitoring at customer	1 x cable gland M20	SMART	EHO860-11730692	
		1 x flange connector M23	SMART	EHO860-11730693	
Cone shaft ø17 mm	1024, HTL-P	1 x cable gland M20	Manipulation proof	EHO860-11730694	
		1 x flange connector M23	Manipulation proof	EHO860-11730695	
	2048, HTL-P	1 x cable gland M20	Manipulation proof	EHO860-11730696	
		1 x flange connector M23	Manipulation proof	EHO860-11730697	
	Parameterization at factory ¹⁾	1 x cable gland M20	Manipulation proof	EHO860-11730698	
		1 x flange connector M23	Manipulation proof	EHO860-11730699	
Parameterization & monitoring at customer	1 x cable gland M20	SMART	EHO860-11730701		
	1 x flange connector M23	SMART	EHO860-11730702		

1) Please choose resolution, output stage and zero pulse (length and position) with your order

Resolution: 1...32768 ppr

Output stage: HTL-P or TTL

Zero pulse:

- 90°, K1=K2=1

- 180°, K1=0

- 180°, K2=0

- 180°, K1=1

Example for EHO860 - 11730674: 5000 ppr, TTL, 180°, K2=0