


**Vue d'ensemble**

- M12, male, A-coded, 4-poles; PUR, 200 cm; M12, female, 90°, A-coded, 4-poles
- Dragchain capable, suitable for robotics  $\pm 180$  °/m
- Head A: IP65, IP66K, IP67
- Cable: good resistance against chemicals, flames and oils
- Halogen free



**Caractéristiques techniques**

**Side A**

Head A: Connection	M12
Head A: Angle cable outlet	0°
Head A: Gender	Male
Head A: Coding	A
Head A: No. of poles	5
Head A: LED	No
Head A: Width across flats	AF14
Head A: Tightening torque	0,6 Nm
Head A: Knurled nut material	Stainless steel (V4A)
Head A: Body color	Blue
Labeling sleeve side A	No

**Side B**

Head B: Connection	M12
Head B: Angle cable outlet	90°
Head B: Gender	Female
Head B: Coding	A
Head B: No. of poles	5
Head B: LED	No
Head B: Width across flats	AF14
Head B: Knurled nut material	Stainless steel (V4A)
Head B: Body color	Blue
Head B: Gasket material	EPDM
Labeling sleeve side B	No

**Cables**

Cable length	200 cm
Shielded	No
AWG	22
External sheath: Material	TPE-S
External sheath: Color	Blue

**Cables**

Wire cross section	0,34 mm <sup>2</sup>
--------------------	----------------------

**Cable**

Shielded	No
Cable length	200 cm
AWG	22
Torsion speed	max. 35 cycles/min
Conductor: Material	Copper, bare
External sheath: Material	TPE-S
Insulation: Material	PP
Paired stranding	No
Torsion stress in °	$\pm 180$ °/m
Total stranding	5 wires strand around core-filler
Wire cross section	0,34 mm <sup>2</sup>
Wire processing	No
External sheath: Color	Blue

**Données mécaniques**

Head A: Degree of protection	IP65, IP68, IP69K
Head B: Degree of protection	IP65, IP68, IP69K
Torsion speed	max. 35 cycles/min
Torsion stress in °	$\pm 180$ °/m

**Conditions ambiantes**

Dragchain capable	Oui
Head A: Chemical resistance	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head A: Flame resistance	HB (UL 94)

**Caractéristiques techniques**
**Conditions ambiantes**

Head A: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.
Head A: Acid and alkali resistant	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head A: Pollution degree	3
Head B: Chemical resistance	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head B: Flame resistance	HB (UL 94)
Head B: Oil resistance	Good resistance to ASTM 1 oil and mineral oils. Limited resistance to hydraulic oils. If other oils are used, the resistance must be checked in relation to the application.

**Conditions ambiantes**

Head B: Acid and alkali resistant	Chemical resistance tested according to ECOLAB. If other media are used, the material resistance must be tested according to the application.
Head B: Pollution degree	3
Cable: Acid and alkali resistant	Good (analogue FDA 21 178.3620, 178.3297, 177.1520)
Cable: Silicone-free	Oui

**Commercial data**

Eclass	27060311
--------	----------