

FHDM 16P5001

Diffuse sensors with background suppression - standard

Article number: 10232117

Overview

- background suppression
- 20 ... 450 mm
- pulsed red LED
- PNP
- mechanical, 5 turn
- cable 4 pin, 2 m
- -25 ... 65 °C
- IP 67



Picture similar



Technical data

General data

Type	Background suppression
Light source	Pulsed red LED
Sensing distance T_w	20 ... 450 mm
Sensing range T_b (at T_w max.)	20 ... 450 mm
Sensing range T_b (at T_w min.)	5 ... 20 mm
Light indicator	LED yellow
Sensing distance adjustment	Mechanical, 5 turn
Wave length	660 nm
Suppression of reciprocal influence	Yes

Electrical data

Response time / release time	< 1 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	41 mA

Electrical data

Current consumption typ.	29 mA
Voltage drop V_d	< 1.8 VDC
Output function	Light / dark operate
Output circuit	PNP
Output current	< 200 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

Mechanical data

Width / diameter	15.4 mm
Height / length	50 mm
Depth	50 mm
Type	Rectangular
Housing material	Die-cast zinc
Front (optics)	PMMA
Connection types	Cable 4 pin, 2 m

Ambient conditions


Protection class	IP 67
Operating temperature	-25 ... +65 °C

FHDM 16P5001

Diffuse sensors with background suppression - standard

Article number: 10232117

Dimension drawing



- * emitter axis

Connection diagram

