

Overview

- IP67 field IO-Link Master
- 8 Ports, Class A/B, up to 4 A per port, 400 µs cycle time
- Industrial Ethernet: EtherNet/IP
- IIoT: OPC UA, MQTT, JSON REST API



Technical data

General data

Degree of protection	IP67
LED Indicators	Digital Input Ethernet Port Status IO-Link Module status Network status Power supply

Communication Interfaces

Communication Interfaces	Ethernet IO-Link
Protocols	EtherNet/IP™ OPC UA MQTT JSON

Software

Baumer Sensor Suite

Electrical data

Connector	Female M12 5-Pol, A-coded Female M12 4-Pole, D-coded Male M12 5-Pol, L-coded, (Supply input) Female M12 5-Pol, L-coded, (Supply output)
Power supply	24 V DC
Power Consumption	0.18 A
Current supply	US 16 A (Master and Sensors) UA 16 A (Actuators)

Communication interface Ethernet

Number of connections	2
Connector	Female M12 4-Pole, D-coded
Standards	IEEE 802.3: 10Base-T / IEEE 802.3u: 100Base-TX
Transmission rate	10 MBit/s 100 MBit/s
Cable length	100 m

Communication interface Ethernet

Protocols	EtherNet/IP™ OPC UA MQTT JSON
-----------	--

Communication interface IO-Link

IO-Link port type	Class A/B
Number of connections	8
Number of input and outputs	8 x IO-Link Digital Input (DI) Digital Output (DO)
Output current L+/L-	2 A
Output current C/Q	2 A
Output current Master max.	10 A
Short-circuit-proof	Yes
Reverse polarity protected	Yes

Communication interface Digital input

Standards	IEC 61131-2 Typ 1 and Typ 3 conform
-----------	-------------------------------------

Communication interface Digital output

Output voltage	24 V DC
Output current max.	2 A
Output current L+/L-	2 A
Output current C/Q	2 A
Output current Master max.	10 A
Short-circuit-proof	Yes
Reverse polarity protected	Yes

Mechanical data

Model	Cubic
Width	63 mm
Height	225 mm
Depth	36 mm
Weight	470 g

Technical data

Environmental conditions

Operating temperature min. -25 °C ...+ 70 °C

Environmental conditions

Storage temperature min. -25 °C ...+ 85 °C

Connection diagram

Connection diagram

