

Overview

- liquid level sensor
- 3 ... 7 mm
- pulsed infrared diode
- PNP
- no
- cable 3 pin, 2.5 m
- 10 ... 55 °C
- IP 50



Picture similar

Technical data

General data

Type	Liquid level sensor
Light source	Pulsed infrared diode
Output indicator	LED red
Sensitivity adjustment	No
Wave length	950 nm
Max. outer diameter of the pipe / tube	3 ... 7 mm
Max. thickness of the pipe / tube	1 mm

Electrical data

Response time / release time	< 2 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	25 mA
Voltage drop Vd	< 1 VDC

Electrical data

Output function	Light / dark operate switchable
Output circuit	PNP
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes


Mechanical data

Width / diameter	16 mm
Height / length	28 mm
Depth	26 mm
Type	Rectangular
Housing material	PC
Connection types	Cable 3 pin, 2,5 m

Ambient conditions

Operating temperature	-10 ... +55 °C
Protection class	IP 50

Dimension drawing



Connection diagram

