

## FPDM 16N5101/S14

Retro-reflective sensors - standard

Article number: 10232272

### Overview

- retro-reflective sensor
- 7,3 m
- pulsed red LED
- NPN
- no
- connector M12 4 pin
- -25 ... 65 °C
- IP 67



Picture similar



### Technical data

#### General data

Type	Retro-reflective sensor
Light source	Pulsed red LED
Actual range Sb	7.3 m
Nominal range Sn	8.5 m
Polarization filter	Yes
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED yellow
Sensitivity adjustment	No
Wave length	660 nm
Suppression of reciprocal influence	Yes

#### Electrical data

Response time / release time	< 1 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	36 mA

#### Electrical data

Current consumption typ.	26 mA
Voltage drop Vd	< 1.8 VDC
Output function	Light / dark operate
Output circuit	NPN
Output current	< 200 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

#### Mechanical data

Width / diameter	15.4 mm
Height / length	50 mm
Depth	50 mm
Type	Rectangular
Housing material	Die-cast zinc
Front (optics)	PMMA
Connection types	Connector M12 4 pin

#### Ambient conditions


Operating temperature	-25 ... +65 °C
Protection class	IP 67

# FPDM 16N5101/S14

Retro-reflective sensors - standard

Article number: 10232272

## Technical drawings



## Connection diagram

