

FZDK 10N1101/KS35

Diffuse sensors with intensity difference - miniature

Article number: 10147577

Overview

- intensity difference
- 5 ... 200 mm
- pulsed red LED
- NPN
- potentiometer, 270°
- flylead connector M8 3 pin
- -25 ... 65 °C
- IP 65



Picture similar



Technical data

General data

Type	Intensity difference
Light source	Pulsed red LED
Sensing distance Tw	5 ... 200 mm
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED yellow
Sensitivity adjustment	Potentiometer, 270°
Wave length	660 nm
Suppression of reciprocal influence	Yes

Electrical data

Response time / release time	< 1 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	30 mA
Current consumption typ.	20 mA

Electrical data

Voltage drop Vd	< 1.8 VDC
Output function	Light operate
Output circuit	NPN
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

Mechanical data

Width / diameter	10.4 mm
Height / length	27 mm
Depth	14 mm
Type	Rectangular
Housing material	Plastic (ASA)
Front (optics)	PMMA
Connection types	Flylead connector M8 3 pin

Ambient conditions


Protection class	IP 65
Operating temperature	-25 ... +65 °C

FZDK 10N1101/KS35

Diffuse sensors with intensity difference - miniature

Article number: 10147577

Dimension drawing



- * emitter axis

Connection diagram

