

## FZDK 10P5101/S35A

Diffuse sensors with intensity difference - miniature

Article number: 10131281

### Overview

- intensity difference
- 5 ... 200 mm
- pulsed red LED
- PNP
- potentiometer, 270°
- connector M8 4 pin
- -25 ... 65 °C
- IP 67



Picture similar



### Technical data

#### General data

Type	Intensity difference
Light source	Pulsed red LED
Sensing distance Tw	5 ... 200 mm
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED yellow
Sensitivity adjustment	Potentiometer, 270°
Wave length	660 nm
Suppression of reciprocal influence	Yes

#### Electrical data

Response time / release time	< 1 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	30 mA
Current consumption typ.	20 mA

#### Electrical data

Voltage drop Vd	< 1.8 VDC
Output function	Light / dark operate
Output circuit	PNP
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

#### Mechanical data


Width / diameter	10.4 mm
Height / length	27 mm
Depth	14 mm
Type	Rectangular
Housing material	Plastic (ASA)
Front (optics)	PMMA
Connection types	Connector M8 4 pin

#### Ambient conditions

Protection class	IP 67
Operating temperature	-25 ... +65 °C

# FZDK 10P5101/S35A

## Dimension drawing



- \* emitter axis

## Connection diagram

