

## FZDM 08P3001

Diffuse sensors with intensity difference - subminiature

Article number: 10219185

### Overview

- intensity difference
- < 40 mm
- pulsed infrared diode
- PNP
- no
- cable 3 pin, 2 m
- -25 ... 65 °C
- IP 65



Picture similar



### Technical data

#### General data

Type	Intensity difference
Light source	Pulsed infrared diode
Sensing distance $T_w$	< 40 mm
Alignment / soiled lens indicator	Flashing light indicator
Light indicator	LED red
Sensitivity adjustment	No
Wave length	880 nm
Suppression of reciprocal influence	Yes

#### Electrical data

Response time / release time	< 1 ms
Voltage supply range +Vs	10 ... 30 VDC
Current consumption max. (no load)	42 mA
Current consumption typ.	20 mA

#### Electrical data

Voltage drop $V_d$	< 2 VDC
Output function	Dark operate
Output circuit	PNP
Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

#### Mechanical data

Width / diameter	8 mm
Height / length	58 mm
Depth	12 mm
Type	Rectangular
Housing material	Aluminum anodized
Front (optics)	PC
Connection types	Cable 3 pin, 2 m

#### Ambient conditions


Protection class	IP 65
Operating temperature	-25 ... +65 °C

# FZDM 08P3001

Diffuse sensors with intensity difference - subminiature

Article number: 10219185

## Dimension drawing



## Connection diagram

