

Overview

- 1 mm
- NPN break function (NC)
- cable, 2 m
- -10 ... 70 °C
- IP 67



Picture similar



Technical data

General data

Mounting type	Flush
Nominal sensing distance Sn	1 mm
Temperature drift	- 5 % / + 10 % (+10 ... +60 °C) - 5 % / + 15 % (-10 ... +70 °C)
Hysteresis	2 ... 20 % of Sr
Output indicator	LED red

Electrical data

Switching frequency	4 kHz
Voltage supply range +Vs	6 ... 30 VDC
Current consumption max. (no load)	10 mA
Output circuit	NPN break function (NC)
Voltage drop Vd	< 2 VDC

Electrical data

Output current	< 100 mA
Short circuit protection	Yes
Reverse polarity protection	Yes

Mechanical data

Type	Cylindrical smooth
Material (sensing face)	POM
Housing material	Stainless steel
Dimension	3 mm
Housing length	16 mm
Connection types	Cable, L=2 m


Ambient conditions

Operating temperature	-10 ... +70 °C
Protection class	IP 67

Remarks

- Fully contained
- Cable version: 16 mm housing length
- Individual strands: 12 mm housing length

Dimension drawing



Connection diagram

