

LXG-80C

Dual GigE, 8 Megapixel, Color

Article number: 11125118

Overview

- 3360 × 2496 px
- ams (CMOSIS) CMV8000
- 4/3" CMOS
- 29 fps
- Dual Gigabit Ethernet



Picture similar



GEN<i>i>CAM



Technical data

Sensor information

Sensor	ams (CMOSIS) CMV8000
Mono/Color	Color
Color filter	RGB Bayer Mosaic
Sensor type	4/3" CMOS
Shutter type	Global shutter
Resolution	3360 × 2496 px
Pixel size	5.5 × 5.5 µm
Exposure time	0.04 ... 1000 ms

Data quality (EMVA 1288 typical)

Dark noise	12.88 e-
Saturation capacity	9378 e-
Dynamic range	56.9 dB
Signal-to-noise ratio	39.7 dB
Quantum efficiency	34.7 % @ 465 nm 34.7 % @ 536 nm 34.2 % @ 631 nm

Acquisition formats

Image formats, interface frame rate max.	Full Frame, 3360 × 2496 px, max. 29 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 3360 × 2496 px, max. 61 fps
Pixel formats	BayerGB8 BayerGB12 BayerGB12 Packed

Image preprocessing

Analog controls	Gain (0 ... 12 dB) Offset (0 ... 255 LSB 12 Bit)
-----------------	---

Color models	Raw Bayer
--------------	-----------

Camera features

Synchronization	free running trigger
Trigger sources	Hardware Software ActionCommand
Trigger delay	0 ... 2 sec, tracking and buffering of up to 256 trigger signals
Sequencer	Automated control for series of images using different sets of parameters
Sequencer parameter	Exposure time gain factor Output ROI Offset x ROI Offset y
Digital inputs	1 input line
Digital outputs	3 output lines
Internal image buffer	512 MB
Interfaces and connectors	
Data interface	Dual Gigabit Ethernet, Transfer rate 2000 Mbits/sec, Connector: 2 x 8P8C Modular Jack (RJ45), screwable type
Process interface	M8 / 8 pins
Power supply	via M8 / 8 pins

LXG-80C

Dual GigE, 8 Megapixel, Color

Article number: 11125118

Technical data

Mechanical data

Lens mount	M58-mount (F-mount, M42, C-mount via adapter)
Width	60 mm
Height	60 mm
Depth	54.25 mm
Weight	≤ 290 g (M58-mount)
Material	housing: aluminum

Electrical data

Voltage supply range +Vs	12 ... 24 V DC (external power supply) 36 ... 57 V DC (Power over Ethernet)
Power consumption	Approx. 7.2 W @ 24 VDC Approx. 7.2 W @ 48 VDC (PoE)

Non-volatile memory

Flash memory size	128 kB
-------------------	--------

Environmental conditions

Operating temperature	+5 ... +66 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

Conformity

Conformity	CE RoHS EAC BIS-CRS (R-41207004)
------------	---

Dimension drawing

