

# TYPE APPROVAL CERTIFICATE

## This is to certify:

That the **Miscellaneous Transmitter**

with type designation(s)  
**PAC50S and PAC50H conductivity sensor/transmitter**

Issued to

**Baumer A/S**  
**Aarhus V, Denmark**

is found to comply with  
**DNV rules for classification – Ships, offshore units, and high speed and light craft**

## Application :

Product(s) approved by this certificate is/are accepted for installation on all vessels classed by DNV.

## Location classes:

Temperature	D
Humidity	B
Vibration	B / C ( $\pm 2.5$ mm / 4.0 g up to 100 Hz)
EMC	B
Enclosure	B / IP67 / IP69k

Issued at **Høvik** on **2022-12-02**

for **DNV**

This Certificate is valid until **2027-12-01**.

DNV local unit: **Denmark CMC**

Approval Engineer: **Ståle Sneen**

\_\_\_\_\_  
**Frederik Tore Elter**  
**Head of Section**

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



## Product description

PAC50S (standard) and PAC50H (hygienic) conductivity sensor/transmitter.

### Ordering key:

- PAC50S-1430A.32D1##.A04305.1000
- PAC50H-1430A.32D1##.A04304.1030

### ## in the ordering key denotes different variants:

- 0# Without display
- 1# With display
- #A 37 mm, standard probe orientation
- #B 60 mm, standard probe orientation
- #C 83 mm, standard probe orientation
- #D 37 mm, 90° rotated probe orientation
- #E 60 mm, 90° rotated probe orientation
- #F 83 mm, 90° rotated probe orientation

### Technical data:

Min. measurable conductivity	1 µS/cm
Max. measuring span	1000 mS/cm
Max. measuring error	≤ ±2.0 % MV ±15 µS/cm
Reference conditions for max. measuring error	Sensor incl. transmitter @ 25°C ambient temperature
Process connection	G 1 A hygienic
Housing material	AISI 316L (1.4404)
Electrical connection	Connector M12-A, 5-pin, stainless steel
Voltage supply range	11...35 V DC
	18...30 V DC, with IO-Link
Current consumption (no load)	12 mA, typ.
	30 mA, max.
Output signals	Switching output, 4...20 mA, IO-Link interface

See website [www.baumer.com](http://www.baumer.com) for configuration possibilities and further technical data.

## Approval conditions

The Type Approval covers hardware listed under Product description. When the hardware is used in applications to be classed by DNV, documentation for the actual application is to be submitted for approval by the manufacturer of the application system in each case. Reference is made to DNV rules for classification of ships Pt.4 Ch.9 Control and monitoring systems.

## Type Approval documentation

Name / description	Doc. No.	Revision / Date
Data sheet: Baumer PAC50H (PAC50H-1430A.32D1##.A04304.1030)	-	- / 2022-10-24
Data sheet: Baumer PAC50S (PAC50S-1430A.32D1##.A04305.1000)	-	- / 2022-10-24
Test report: RISE Classification of degree of protection provided by enclosure	O197977	- / 2022-01-26
Test report: Baumer PAC50 EMC test report	81392760	01 / 2022-11-14
Test report: Baumer PAC50 Pressure test report	81411535	00 / 2022-11-14
Test report: EKTOS TA test of PAC50S sensor according to DNV-CG-0339:2021	P22-0132	1 / 2022-11-15

## Tests carried out

Applicable tests according to class guideline DNV-CG-0339, August 2021.  
 200% hydrostatic pressure test (test pressure 50 bar for 5 minutes).

## Marking of product

The products to be marked with:

- manufacturer name
- model name
- serial number
- power supply ratings

### **Periodical assessment**

The scope of the periodical assessment is to verify that the conditions stipulated for the type are complied with, and that no alterations are made to the product design or choice of systems, software versions, components and/or materials.

The main elements of the assessment are:

- Ensure that type approved documentation is available
- Inspection of factory samples, selected at random from the production line (where practicable)
- Review of production and inspection routines, including test records from product sample tests and control routines
- Ensuring that systems, software versions, components and/or materials used comply with type approved documents and/or referenced system, software, component and material specifications
- Review of possible changes in design of systems, software versions, components, materials and/or performance, and make sure that such changes do not affect the type approval given
- Ensuring traceability between manufacturer's product type marking and the type approval certificate

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE