


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for “Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)” (see www.standard1288.org or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 RGB Release 3, 15.08.2015, SN 0001(Baumer), recalibrated 28.08.2017 . The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.



Vendor	Baumer
Model	LXG-200M.P
Serial number	1289103317
Sensor diagonal	34.33 mm
Lens category	M58 mount
Resolution	4288 × 3224, 12 bit
Pixel size	6.40 μm × 6.40 μm
Sensor	CMOSIS CMV20000
Sensor type	CMOS
Shutter type	Global shutter
Overlap capabilities	Overlapped
Maximum frame rate	0.0 Hz
Interface type	GEV

Type of data presented	Single
Operation point 1	
Wavelength centroid	535.8 nm
Wavelength FWHM	31.9 nm
Gain / BlackLevel	1.0 / 80.0
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain / BlackLevel	1.0 / 80.0
Exposure control	By irradiance	Environmental temperature	24.3°C
Exposure time	579.00 μ s	Camera body temperature	36.2°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono12Packed	Wavelength, centr., FWHM	536 nm, 31.9 nm



Quantum efficiency

η 76.8%

Overall system gain

K 0.255 DN/e⁻
 $1/K$ 3.916 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 2.83 DN
 DSNU₁₂₈₈ 4.82 DN
 σ_d 11.03 e⁻
 DSNU₁₂₈₈ 18.88 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 123
 41.8 dB
 6.9 bit
 $1/\text{SNR}_{\text{max}}$ 0.82 %
 PRNU₁₂₈₈ 1.50 %

Nonlinearity

LE 0.46%
 LE_{min} -0.39%
 LE_{max} 0.54%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 15.1 p
 0.37 p/ μm^2
 $\mu_{p,\text{sat}}$ 19577 p
 478 p/ μm^2
 $\mu_{e,\text{min}}$ 11.6 e⁻
 0.28 e⁻/ μm^2
 $\mu_{e,\text{sat}}$ 15028 e⁻
 367 e⁻/ μm^2

Dynamic range

DR 1296
 62.2 dB
 10.3 bit

Dark current

$\mu_{c,\text{mean}}$ 171.7 DN/s
 $\mu_{c,\text{mean}}$ 672.4 e⁻/s
 $\mu_{c,\text{var}}$ 350.9 e⁻/s