

## VEXU-24C

USB 3.0, 2,3 Megapixel, Color

Article number: 11151568

### Overview

- 1920 × 1200 px
- Sony IMX249
- 1/1.2" CMOS
- 38 fps
- USB 3.0



Picture similar



GEN*i*CAM



### Technical data

#### Sensor information

Sensor	Sony IMX249 Gen1
Mono/Color	Color
Sensor type	1/1.2" CMOS
Shutter type	Global shutter
Resolution	1920 × 1200 px
Pixel size	5.86 × 5.86 μm
Exposure time	0.057 ... 60000 ms

#### Data quality (EMVA 1288 typical)

Dark noise	7.41 e-
Saturation capacity	32014 e-
Dynamic range	71.7 dB
Signal-to-noise ratio	45.1 dB
Quantum efficiency	55.8 % @ 465 nm 61.5 % @ 536 nm 47.2 % @ 631 nm

#### Acquisition formats

Image formats, interface frame rate max.	Full Frame, 1920 × 1200 px, max. 38 fps Binning 2×2, 960 × 600 px, max. 38 fps Binning 2×1, 960 × 1200 px, max. 38 fps Binning 1×2, 1920 × 600 px, max. 38 fps
Image formats, acquisition frame rate max. (Burst Mode)	Full Frame, 1920 × 1200 px, max. 38 fps
Pixel formats	BayerRG8 BayerRG12

#### Image preprocessing

Analog controls	Gain (0 ... 48 dB) Offset (0 ... 255 LSB 12 Bit)
-----------------	---

Color models	Raw Bayer
--------------	-----------

#### Camera features

Basic Functions	Exposure Gain / Color Gain Trigger / Exposure Active (Flash) Binning 2x2 Partial Scan Offset Free Running Mode (Live Image)
-----------------	---

Acquisition / Interface	Adjustable Framerate
-------------------------	----------------------

Synchronization	free running trigger
-----------------	-------------------------

Trigger sources	Hardware Software
-----------------	----------------------

Process Synchronization	Debouncer
-------------------------	-----------

Additional Functions	User Set
----------------------	----------

Internal image buffer	0 MB
-----------------------	------

#### Interfaces and connectors

Data interface	USB 3.0, Transfer Rate 5000 Mbits/sec, Connector: USB 3.0 Micro B
----------------	--

Process interface	M8 / 4 pins (SACC-DSI-M 8MS-4CON-L180)
-------------------	--

Power supply	via USB 3.0 interface
--------------	-----------------------

#### Mechanical data

Lens mount	CS-mount
------------	----------

## VEXU-24C

USB 3.0, 2,3 Megapixel, Color

Article number: 11151568

### Technical data

#### Mechanical data

Width	29 mm
Height	29 mm
Depth	38 mm
Weight	≤ 90 g
Material	zinc die casting, nickel-plated, IP 40

#### Electrical data

Power consumption	Approx. 1.5 W @ 38.0 fps
Operating voltage	5 VDC (via USB3.0 interface)

#### Non-volatile memory

Flash memory size	128 kB
-------------------	--------

#### Environmental conditions

Operating temperature	+5 ... +65 °C @ T = measurement point
Humidity	10 ... 90 % (non-condensing)
Protection class	IP 40

#### Digital I/Os

Lines	1 input line 1 output line
-------	-------------------------------

#### Conformity

Conformity	CE RoHS EAC
------------	-------------------

### Dimension drawing

