


Fork and angle sensors

FGUM 120P8001/S35L

dimension drawing



general data

type	through beam sensor
object size	> 0,8 mm
repeatability	< 0,06 mm
hysteresis	< 0,25 mm
ambient light immunity	50 kLux
sensitivity adjustment	Pot, 270°
light source	pulsed red LED
wave length	660 nm
light indicator	LED yellow

electrical data

response time / release time	< 0,25 ms
switching frequency	< 2 kHz
voltage supply range +Vs	10 ... 35 VDC
current consumption max.	40 mA
output function	light / dark operate switchable
output circuit	PNP
voltage drop Vd	< 2,8 VDC
output current	< 200 mA
short circuit protection	yes
reverse polarity protection	yes

mechanical data

width / diameter	144 mm
fork width Sb	120 mm
height / length	90 mm
penetration depth	60 mm
depth	12 mm
type	U profile
housing material	die-cast zinc
connection types	connector M8, 3 pin


ambient conditions

operating temperature	-10 ... +60 °C
protection class	IP 67

photo



connection diagram



- accessories: PNP/NPN - converter