




EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at www.standard1288.org and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 7, 21.08.2018, SN 0018(AEON).

Measurements performed by Technical and Application Support Center, Baumer Optronic GmbH.

| | | | |
|------------------|------------------------|-------------------------------|------------|
| Vendor | Baumer | Type of data presented | Single |
| Model | VCXG.2-65C.R | Operation point 1 | |
| Serial number | 700009691989 | Wavelength centroid | 467.2 nm |
| Sensor diagonal | 8.86 mm | Wavelength FWHM | 19.5 nm |
| Lens category | C-Mount | Gain, black-level | 1.0 / 40.0 |
| Resolution | 3072 × 2048, 12 bit | Operation point 2 | |
| Pixel size (h×v) | 2.40 μm × 2.40 μm | Wavelength centroid | 533.3 nm |
| Sensor | Sony IMX178 | Wavelength FWHM | 30.3 nm |
| Sensor type | CMOS | Gain, black-level | 1.0 / 40.0 |
| Shutter type | Rolling shutter | Operation point 3 | |
| Overlap cap. | Overlapped | Wavelength centroid | 629.9 nm |
| Max. frame rate | 0.0 Hz | Wavelength FWHM | 12.9 nm |
| Interface type | GEV | Gain, black-level | 1.0 / 40.0 |
| | | Optional data measured | |
| | | None | |






Summary Sheet for Operation Point 1 at a Wavelength of 467 nm

| | | | |
|--------------------|---------------|---------------------------|-----------------|
| Type of data | Single | Gain, black-level | 1.0 / 40.0 |
| Exposure control | By irradiance | Environmental temperature | 24.6 °C |
| Exposure time | 1.60 ms | Camera body temperature | 29.4 °C |
| Frame rate | 9.6 Hz | Internal temperature(s) | — |
| Data transfer mode | BayerRG12 | Wavelength, centr., FWHM | 467 nm, 19.5 nm |


Photon Transfer

Photon transfer mACC300243, 467 nm, 09.10.2023



Signal-to-Noise Ratio

SNR mACC300243, 467 nm, 09.10.2023



| | | |
|---------------------------------------|-----------------------------|----------------------------------------|
| Quantum efficiency | η | 59.1% |
| Overall system gain | K | 0.271 DN/e ⁻ |
| | $1/K$ | 3.697 e ⁻ /DN |
| Temporal dark noise | σ_d | 3.41 e ⁻ |
| | $\sigma_{y,\text{dark}}$ | 0.97 DN |
| Signal-to-noise ratio | SNR_{max} | 121 |
| | | 41.6 dB |
| | | 6.9 bit |
| | $1/\text{SNR}_{\text{max}}$ | 0.83 % |
| Absolute sensitivity threshold | $\mu_{p,\text{min}}$ | 6.95 p |
| | $\mu_{p,\text{min,area}}$ | 1.207 p/ μm^2 |
| | $\mu_{e,\text{min}}$ | 4.11 e ⁻ |
| | $\mu_{e,\text{min,area}}$ | 0.713 e ⁻ / μm^2 |
| Saturation capacity | $\mu_{p,\text{sat}}$ | 24713 p |
| | $\mu_{p,\text{sat,area}}$ | 4290 p/ μm^2 |
| | $\mu_{e,\text{sat}}$ | 14606 e ⁻ |
| | $\mu_{e,\text{sat,area}}$ | 2536 e ⁻ / μm^2 |
| Dynamic range | DR | 3555 |
| | | 71.0 dB |
| | | 11.8 bit |
| Spatial nonuniformities | DSNU_{1288} | 0.15 e ⁻ |
| | | 0.04 DN |
| | PRNU_{1288} | 0.43 % |
| Linearity error | LE_{min} | -0.29% |
| | LE_{max} | 0.87% |
| Dark current | $\mu_{c,\text{mean}}$ | 0.20 ± 0.02 e ⁻ /s |
| | | 0.05 DN/s |
| | $\mu_{c,\text{var}}$ | 0.39 ± 0.06 e ⁻ /s |
| | T_d | — °C |




Summary Sheet for Operation Point 2 at a Wavelength of 533 nm

| | | | |
|--------------------|---------------|---------------------------|-----------------|
| Type of data | Single | Gain, black-level | 1.0 / 40.0 |
| Exposure control | By irradiance | Environmental temperature | 24.8°C |
| Exposure time | 3.16 ms | Camera body temperature | 29.6°C |
| Frame rate | 9.6 Hz | Internal temperature(s) | — |
| Data transfer mode | BayerRG12 | Wavelength, centr., FWHM | 533 nm, 30.3 nm |


Photon Transfer

Photon transfer mACC300243, 533 nm, 09.10.2023



Signal-to-Noise Ratio

SNR mACC300243, 533 nm, 09.10.2023



| | | |
|---------------------------------------|--------------------|----------------------------------|
| Quantum efficiency | η | 63.9% |
| Overall system gain | K | 0.271 DN/e ⁻ |
| | $1/K$ | 3.690 e ⁻ /DN |
| Temporal dark noise | σ_d | 3.34 e ⁻ |
| | $\sigma_{y,dark}$ | 0.95 DN |
| Signal-to-noise ratio | SNR_{max} | 120 |
| | | 41.6 dB |
| | | 6.9 bit |
| | $1/SNR_{max}$ | 0.83 % |
| Absolute sensitivity threshold | $\mu_{p,min}$ | 6.33 p |
| | $\mu_{p,min,area}$ | 1.099 p/ μm^2 |
| | $\mu_{e,min}$ | 4.04 e ⁻ |
| | $\mu_{e,min,area}$ | 0.702 e ⁻ / μm^2 |
| Saturation capacity | $\mu_{p,sat}$ | 22621 p |
| | $\mu_{p,sat,area}$ | 3927 p/ μm^2 |
| | $\mu_{e,sat}$ | 14450 e ⁻ |
| | $\mu_{e,sat,area}$ | 2509 e ⁻ / μm^2 |
| Dynamic range | DR | 3574 |
| | | 71.1 dB |
| | | 11.8 bit |
| Spatial nonuniformities | $DSNU_{1288}$ | 0.15 e ⁻ |
| | | 0.04 DN |
| | $PRNU_{1288}$ | 0.48 % |
| Linearity error | LE_{min} | -0.57% |
| | LE_{max} | 0.95% |
| Dark current | $\mu_{c,mean}$ | 0.44 ± 0.02 e ⁻ /s |
| | | 0.12 DN/s |
| | $\mu_{c,var}$ | 0.63 ± 0.07 e ⁻ /s |
| | T_d | — °C |




Summary Sheet for Operation Point 3 at a Wavelength of 630 nm

| | | | |
|--------------------|---------------|---------------------------|-----------------|
| Type of data | Single | Gain, black-level | 1.0 / 40.0 |
| Exposure control | By irradiance | Environmental temperature | 24.8°C |
| Exposure time | 3.16 ms | Camera body temperature | 29.6°C |
| Frame rate | 9.6 Hz | Internal temperature(s) | — |
| Data transfer mode | BayerRG12 | Wavelength, centr., FWHM | 630 nm, 12.9 nm |


Photon Transfer

Photon transfer mACC300243, 630 nm, 09.10.2023



Signal-to-Noise Ratio

SNR mACC300243, 630 nm, 09.10.2023



| | | |
|---------------------------------------|---------------------------|----------------------------------------|
| Quantum efficiency | η | 45.6% |
| Overall system gain | K | 0.271 DN/e ⁻ |
| | 1/ K | 3.691 e ⁻ /DN |
| Temporal dark noise | σ_d | 3.36 e ⁻ |
| | $\sigma_{y,\text{dark}}$ | 0.96 DN |
| Signal-to-noise ratio | SNR _{max} | 120 |
| | | 41.6 dB |
| | | 6.9 bit |
| | 1/SNR _{max} | 0.83 % |
| Absolute sensitivity threshold | $\mu_{p,\text{min}}$ | 8.91 p |
| | $\mu_{p,\text{min,area}}$ | 1.547 p/ μm^2 |
| | $\mu_{e,\text{min}}$ | 4.06 e ⁻ |
| | $\mu_{e,\text{min,area}}$ | 0.705 e ⁻ / μm^2 |
| Saturation capacity | $\mu_{p,\text{sat}}$ | 31782 p |
| | $\mu_{p,\text{sat,area}}$ | 5518 p/ μm^2 |
| | $\mu_{e,\text{sat}}$ | 14498 e ⁻ |
| | $\mu_{e,\text{sat,area}}$ | 2517 e ⁻ / μm^2 |
| Dynamic range | DR | 3568 |
| | | 71.0 dB |
| | | 11.8 bit |
| Spatial nonuniformities | DSNU ₁₂₈₈ | 0.19 e ⁻ |
| | | 0.05 DN |
| | PRNU ₁₂₈₈ | 0.57 % |
| Linearity error | LE _{min} | -0.40% |
| | LE _{max} | 0.58% |
| Dark current | $\mu_{c,\text{mean}}$ | 0.32 ± 0.02 e ⁻ /s |
| | | 0.09 DN/s |
| | $\mu_{c,\text{var}}$ | 0.51 ± 0.07 e ⁻ /s |
| | T_d | — °C |